

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

9.5mm Diameter X 9.5mm FL, MgF₂ Coated, PCX Condenser Lens



Stock #15-528 3-4 DAYS

[Other Coating Options](#)



1



€39,00

ADD TO CART

Qty 1-10

€39,00

Qty 11+

€35,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

9.50

Effective Focal Length EFL (mm):

9.50

Numerical Aperture NA:

0.50

Substrate: Float Glass
Focal Length Tolerance (%): ±7
Coating: MgF₂ (400-700nm)
Coating Specification: R_{avg} ≤ 1.75% @ 400 - 700nm
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 4.70 ±0.2
f#: 1.00
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant