

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

9mm Dia. X 36mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-073 CLEARANCE 3-4 DAYS

[Other Coating Options](#)



1



€19,95

ADD TO CART

Qty 1+

€19,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
9.00 +0.00/-0.10

Effective Focal Length EFL (mm):
36.00

Back Focal Length BFL (mm):
34.89

Coating:
MgF₂ (400-700nm)

Coating Specification:

R _{avg} ≤1.75% @400 - 700nm	
Substrate:	N-BK7
Focal Length Tolerance (%):	±1
Centering (arcmin):	6.00
Edge Thickness ET (mm):	1.15
Radius R ₁ (mm):	18.61
Clear Aperture CA (mm):	≥7.65
f/#:	4.00
Numerical Aperture NA:	0.13
Type:	Plano-Convex Lens

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View