

## 9mm Dia. x 9mm FL, Commercial Grade, Double-Convex Lens



Stock **#27-728** CLEARANCE 3-4 DAYS

- 1 + **€14,95**

ADD TO CART

|        |
|--------|
| Qty 1+ |
| €14,95 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

**Diameter (mm):**  
9.00 +0.00/-0.10

**Back Focal Length BFL (mm):**  
7.86

**Effective Focal Length EFL (mm):**  
9.00

**Coating:**  
Uncoated

**Substrate:** ☐  
N-SK18

|                                                      |
|------------------------------------------------------|
| Centering (arcmin):<br>6.00                          |
| Center Thickness CT (mm):<br>3.50                    |
| Center Thickness Tolerance (mm):<br>±0.10            |
| Edge Thickness ET (mm):<br>1.53                      |
| Radius R <sub>1</sub> (mm):<br>10.77                 |
| Clear Aperture CA (mm):<br>≥7.65                     |
| f##:<br>1.00                                         |
| Focal Length Specification Wavelength (nm):<br>587.6 |
| Focal Length Tolerance (%):<br>±1                    |
| Numerical Aperture NA:<br>0.5                        |
| Type:<br>Double-Convex Lens                          |
| Wavelength Range (μm):<br>0.38 - 2.2                 |

### Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |