

TECHSPEC® 9mm Dia. x -18mm FL, VIS-NIR, Inked, Double-Concave Lens



Stock **#48-700-INK** [CONTACT US](#)

⊖ 1 ⊕ **€52,00**

ADD TO CART

Qty 1-9
€52,00
Qty 10+
€46,75
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00

Effective Focal Length EFL (mm):
-18.00

Substrate: N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -18.49
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 8.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 2.45
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -18.86
Surface Quality: 40-20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View