



Stock #12-691 3-4 DAYS

1

€

€5.402,00

ADD TO CART

Qty 1-4

€5.402,00

Qty 5+

€4.862,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

1319, 1650

Diameter (mm):

39.00

Entrance Beam Diameter, 1/e² (mm):

5.9 - 6.0

Model Number: πShaper 6_6_NIR
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <250
Wavelength Range (nm): 1100 - 1700
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant