

Small X-Y Axis Leadscrew Drive



X-Y Axis Leadscrew Drive Metric Stages



Stock **#36-036** 20+ In Stock

-

1

+

€423^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	€423,00 each
Qty 10+	€373,90 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Metric	
Physical & Mechanical Properties	
Linear (X-Y)	Type of Movement:
Dovetail	Guide System:
24 x 30	Stage Size (mm):
10 (±5)	Travel (mm):
5.8mm Thru	Center Hole:
Brass	Construction:
0.5	Leadscrew Pitch (mm):
3.5	Load Capacity (kg):
0.22	Weight (kg):

Hardware & Interface Connectivity	
-----------------------------------	--

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting	
----------------------	--

(6) M3 x 0.5	Mounting Threads:
--------------	-------------------

Regulatory Compliance	
-----------------------	--

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS

- Locking Knobs for Secure Positioning
 - 0.5mm Travel per Knob Rotation
 - Available with up to 15mm Travel in X and Y with 12mm Travel in Z
- Leadscrew Drive Stages are ideal for a variety of positioning requirements that require high load capacities. Each stage features a leadscrew drive and locking knobs for securing the stage position. A top plate is available for large models ([#58-290](#)) with both M6 and 1/4-20 tapped holes to directly accept posts or post holders. Large models feature an aluminum base plate for easy integration.

TECHNICAL INFORMATION

