

[See all 3 Products in Family](#)

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock #32-306 CLEARANCE **7 In Stock**

⊖ 1 ⊕ €11⁹⁵

ADD TO CART

Volume Pricing

Qty 1+	€11,95 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

6.25 +0.00/-0.05 **Diameter (mm):**

±0.1 **Center Thickness Tolerance (mm):**

1.00 **Centering (arcmin):**

2.86	Edge Thickness ET (mm):
2.30	Center Thickness CT 1 (mm):
0.90	Center Thickness CT 2 (mm):
Optical Properties	
35.00	Effective Focal Length EFL (mm):
N-BK7 / N-SF5	Substrate: <input type="checkbox"/>
5.6	f#:
0.08	Numerical Aperture NA:
Uncoated	Coating:
33.59	Back Focal Length BFL (mm):
632.8	Focal Length Specification Wavelength (nm):
±2	Focal Length Tolerance (%):
23.14	Radius R ₁ (mm):
-14.51	Radius R ₂ (mm):
-38.86	Radius R ₃ (mm):
40-20	Surface Quality:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

Compatible Mounts