

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Allied Vision Alvium Right Angle USB 3.1 Cameras](#)

[See all 128 Products in Family](#)

Allied Vision Alvium 1800 U-501m NIR, 1/2.5" 5MP S-Mount, Right Angle USB 3.1 NIR Camera (Partial Housing)

See More by [Allied Vision](#)



Stock **#19-558** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **€284,00**

ADD TO CART

Qty 1+

€284,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type: NIR Camera
Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium Right Angle
Model Number: 1800 U-501m NIR
Imaging Sensor: ON Semi AR0522
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/2.5"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,592 x 1,944
Pixel Size, H x V (µm): 2.2 x 2.2
Sensing Area, H x V (mm): 5.7 x 4.3
Frame Rate (fps): 68.00
Pixel Depth: 8/10 bit
Exposure Time: 8µs - 0.48s @ 450/375 MBps 13µs - 0.84s @ 200 MBps
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 2.2
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 25 x 32 x 29 (includes connectors and lens mount)
Weight (g): 50
Mount: M12 x 0.5 (S-Mount)
Housing: Partial
Interface Port Orientation: Back Panel (Right Angle)
Dynamic Range (dB): 62
Operating Temperature (°C): +5 to +65
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

