

Allied Vision Alvium G1-811c, 2/3" 8.1MP C-Mount, GigE PoE Color Camera

See More by [Allied Vision](#)



Stock **#23-562** 3-4 DAYS

[Similar Cameras](#)

- 1 +

€1.092,00

ADD TO CART

Qty 1+

€1.092,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer: Allied Vision
Mounting Threads: ¼"-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 32MB
Camera Family: Avium G1
Model Number: Avium G1-811c
Imaging Sensor: Sony IMX546
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 8.10
Pixels (H x V): 2,848 x 2,848
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 7.8 x 7.8
Frame Rate (fps): 14.00
Pixel Depth: 12 Bit
Exposure Time: 50µs - 10s
Connector: GigE, RJ45 with Screw Locks
Power Supply: PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581
Power Consumption (W): External power: 3.7 W at 12 VDC Power over Ethernet: 4.0 W
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 41 x 29 x 29
Weight (g): 65
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): -20 to +50
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 10-pin TFM
Machine Vision Standard: GigE Vision V1.2, GenICam V2.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

