

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Allied vision Guppy Pro F-125 1/3" CCD Color Camera

See More by [Allied Vision](#)



Stock #68-568 [CONTACT US](#)

[Similar Cameras](#)



1



€903,00

ADD TO CART

Qty 1+

€903,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
FireWire.b

Type:
Color Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#68-585](#)

Image Buffer: 64MB
Camera Family: Guppy Pro
Model Number: F-125
Imaging Sensor: Sony ICX445
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 1.20
Pixels (H x V): 1,280 x 960
Pixel Size, H x V (µm): 3.75 x 3.75
Sensing Area, H x V (mm): 4.8 x 3.6
Frame Rate (fps): 31.00
Pixel Depth: 12 bit
Exposure Time: Via Software
Connector: FireWire, IEEE 1394b
Power Supply: Power over FireWire, or with Power Supply Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): <3.5 (12VDC External Power Supply)
GPIOs: 1 configurable opto-coupled input, 3 configurable opto-coupled outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 70
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): +5 to +45
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: IIDC Standard v1.31
Power Requirement: Supplied via IEEE-1394 cable or 12-pin Hirose

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

