

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Basler ace2 USB 3.0 Cameras](#)

[See all 30 Products in Family](#)

Basler ace2 a2A5320-23ucPRO Color USB3 Pro Camera



Basler ace2 USB 3.0 Cameras (Front)



Stock **#16-638** 3-4 DAYS

[Similar Cameras](#)

- 1 +

€1.719,00

ADD TO CART

Qty 1+

€1.719,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
Basler

Mounting Threads: ¼-20 with Tripod Mount Adapter #16-641
Image Buffer: Not Specified
Camera Family: ace2
Model Number: a2A5320-23ucPRO
Imaging Sensor: Sony IMX542
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 16.10
Pixels (H x V): 5,320 x 3,032
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 14.6 x 8.3
Frame Rate (fps): 23.00
Pixel Depth: 8/10/12 bit
Exposure Time: Freely Programmable
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): 4.3
GPIOs: 1 opto-coupled input line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 36.3 x 29 x 29 (excludes connectors and lens mount)
Weight (g): <90
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.8
Operating Temperature (°C): -10 to +60
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin MB
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant