

BFS-U3-20S4M-C, USB 3.1 Blackfly® S, Monochrome Camera

See More by [FLIR](#)



FLIR Blackfly® S USB3 Camera (front)



Stock **#22-092** 3-4 DAYS



1



€912,00

ADD TO CART

Qty 1+

€912,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer: FLIR
Mounting Threads: 1/4-20 with Tripod Mount Adapter #15-838
Image Buffer: 240MB
Camera Family: Blackfly® S
Model Number: BFS-U3-20S4M-C
Imaging Sensor: Sony IMX422
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.7"
Resolution (MegaPixels): 2.00
Pixels (H x V): 1,616 x 1,240
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 7.27 x 5.58
Frame Rate (fps): 175.00
Pixel Depth: 10/12 bit
Exposure Time: 9µs - 30s
Connector: USB 3.1 Gen 1, Micro-B with Screw Locks
Power Supply: Power over USB or via GPIO with #88-063
Power Consumption (W): 4.2
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 39 (excludes connectors and lens mount)
Weight (g): 53
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.8
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

