

Blue 300 x 300 Flat Dome Light



Effilux Flat Dome Lights

Stock **#22-110** **1 In Stock**

-

1

+

€1.413⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.413,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
EFFI-FD-300-300-465	Model Number:
LED Illuminator	Type of Illumination:
Effilux	Manufacturer:
	Geometry:

Flat Dome Light	
Constant	Illumination Mode:
Physical & Mechanical Properties	
339 x 339 x 43.2	Dimensions (mm):
3500	Weight (g):
300 x 300	Active Area (mm):
Optical Properties	
Blue	Color:
465	Wavelength (nm):
Electrical	
65	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #73-409 Korea: #73-409 China: #15-874	
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

Effilux Flat Dome Lights achieve diffuse illumination similar to standard dome lights but with a thinner, more compact housing. These flat dome lights provide a large imaging area for increased depth of focus and field of view. The convenient integrated analog controller allows precise control of power and intensity without the need for additional components. Effilux Flat Dome Lights offer greater than 90% uniformity and feature an anti-reflection system that absorbs unwanted light. Flat Dome Lights are ideal for imaging textured, shiny, or uneven surfaces.