

Blue M105 x 1.00 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-605 3-4 DAYS



1



€809,00

ADD TO CART

Qty 1-9

€809,00

Qty 10+

€768,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-400, 550-1212

Clear Aperture CA (mm):
100.00

Coating:
Hard Coated

Filter Thread: M105 x 1.00
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 5.7
Mount Thickness Including Threads (mm): 8.5
Outer Diameter (mm): 109.80
Substrate Thickness (mm): 1.8
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
