

## Blue M67 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-452** [CONTACT US](#)



1



€309,00

ADD TO CART

Qty 1-9

€309,00

Qty 10+

€293,80

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Blocking Wavelength Range (nm):**  
200-400, 550-1203

**Clear Aperture CA (mm):**  
62.50

**Coating:**  
Hard Coated

|                                                        |
|--------------------------------------------------------|
| <b>Filter Thread:</b><br>M67 x0.75                     |
| <b>Color:</b><br>Blue                                  |
| <b>Center Wavelength CWL (nm):</b><br>470.00           |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Full Width-Half Max FWHM (nm):</b><br>85.00         |
| <b>Mount Thickness (mm):</b><br>6.0                    |
| <b>Mount Thickness Including Threads (mm):</b><br>8.3  |
| <b>Outer Diameter (mm):</b><br>70.00                   |
| <b>Substrate Thickness (mm):</b><br>1.3                |
| <b>Type:</b><br>Mounted Imaging Filter                 |
| <b>Minimum Transmission (%):</b><br>≥85                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |