

## C-CLamp



#58-080

Stock **#58-080** [CONTACT US](#)

- 1 + €20<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€20,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Accessory **Type of Illumination:**

#### Regulatory Compliance

[View](#) **Certificate of Conformance:**

# Product Details

Gooseneck quartz halogen illuminators feature a 12V/20W Halogen bulb housed in a high impact, polyamide housing. A heat dissipating Dichroic reflector and clear lens provide a wide angle illumination (flood) or a narrow spot. The lamphead is mounted on a 700 or 500mm gooseneck arm that easily adjusts to any angle. Lamps can be secured directly to a bench or can be mounted on a table top base or an adjustable C-clamp, listed below.

---

;