

[See all 10 Products in Family](#)

C-Mount, X-Y Translating Optic Mount



5 Axes Optical Mount



Stock #87-209 [CONTACT US](#)

- 1 + €371.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€371,00 each
Qty 5-9	€333,90 each
Qty 10+	€307,40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Adjustable - Linear (XY)

Type:

C-Mount

Type of Optics:

Physical & Mechanical Properties

1" x 32 TPI **Clear Aperture CA (mm):**

64.0 **Outer Diameter (mm):**

20.00 **Thickness (mm):**

±1.5 in X and Y **Travel (mm):**

180 **Weight (g):**

Black Anodized Aluminum **Construction:**

Threading & Mounting

Thickness of Compatible Optics (mm):
Dependent on the C-Mount Circular Optic Mount used

M6 x 1.0 **Compatible Post:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 247:**

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

