

Coarse Movement, 50mm Diameter Thru Hole, Rack & Pinion



50mm Diameter Thru Hole

Stock **#03-609** **17 In Stock**

⊖ 1 ⊕ €400⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€400,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rack and Pinion Mount **Type:**

50 mm Diameter Thru-Hole **Note:**

Coarse Movement **Type of Adjustment:**

Physical & Mechanical Properties

Dimensions (mm):

Rack and Pinion Block: 50.8 H x 28.6 W x 50.8 L

2.00 **Load Capacity (kg):**

35 (+23/-12) in Y **Travel (mm):**

25.5 **Travel Per Knob Rotation (mm):**

1.31 **Weight (lbs):**

Linear (Y) **Type of Movement:**

100.00 **Optical Centerline from Post (mm):**

Threading & Mounting

Mounting Post Hole and Thread:
3/4" Diameter Post
1/4-20 Tapped Hole

Regulatory Compliance

Exempt **RoHS 2015:**

Contains SVHC(s) **Reach 224:**

View **Certificate of Conformance:**

Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion. [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.