

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



65mm Diameter Thru Hole

Stock #39-357 3-4 DAYS



1



€434,00

ADD TO CART

Qty 1+

€434,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):

Rack and Pinion Block: 63.5 H x31.75 Wx63.5 L

Travel (mm):

57.15 in Y

Type:

Rack and Pinion Mount

Weight (lbs):

1.5

Travel Per Knob Rotation (mm):

25.5
Load Capacity (kg): 2.00
Note: 65 mm Diameter Thru-Hole
Type of Movement: Linear (Y)
Type of Adjustment: Coarse Movement
Optical Centerline from Post (mm): 110.00
Mounting Post Hole and Thread: 3/4" Diameter Post 5/16-18 Tapped Hole

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View