


## Coarse/Fine Movement, 1/4-20, Rack & Pinion



#54-794

Stock **#54-794 3 In Stock**

€580<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€580,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Rack and Pinion Mount **Type:**

1/4-20 Stud **Note:**

Coarse/Fine Movement **Type of Adjustment:**

### Physical & Mechanical Properties

**Dimensions (mm):**

Rack and Pinion Block: 50 H x 30 W x 50 L

**Load Capacity (kg):**  
2.00

**Travel (mm):**  
35 (+23/-12) in Y

**Travel Per Knob Rotation (mm):**  
25.5 coarse, 3.2 fine

**Type of Movement:**  
Linear (Y)

**Optical Centerline from Post (mm):**  
51.00

## Threading & Mounting

**Mounting Post Hole and Thread:**  
3/4" Diameter Post  
1/4-20 Tapped Hole

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Reach 224:**  
[Contains SVHC\(s\)](#)

**Certificate of Conformance:**  
[View](#)

## Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion. [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.