

Coherent® High Power Water-Cooled Thermopile Sensor PM6K+ 1402728 | 6kW Max Power

See More by [Coherent®](#)



Stock **#12-408** [CONTACT US](#)

- 1 + **€4.730,00**

ADD TO CART

Qty 1+
€4.730,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):

50

Model Number:

1402728

Type:

[Meter required](#)

Computer Interface:

DB-25
Calibration Uncertainty (%): 3
Calibration Wavelength (nm): 1070
Cooling Method: Water
Power Resolution (W): 1
Response Time (s): 20 5s if Speed-up is on
Power Range: 10W-5kW
Compatible Meters: #35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412 , #23-660 , #23-661
Wavelength Range (nm): 250 - 11000
Wavelength Range (µm): 0.25 - 11
Maximum Incident Energy Density: 600mJ/cm ² (10ns, 1064nm)
Maximum Power (W): 6000
Minimum Power (W): 10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View