

Cyan M72 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-589 3-4 DAYS



1



€346,00

ADD TO CART

Qty 1-9

€346,00

Qty 10+

€328,80

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-450, 600-1011

Clear Aperture CA (mm):
67.50

Coating:
Hard Coated

Filter Thread: M72 x0.75
Color: Cyan
Center Wavelength CWL (nm): 505.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 90.00
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3
Outer Diameter (mm): 75.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
