

[See all 4 Products in Family](#)

Dual Axis Linear Scale Micrometer on Opal Glass



Stock #58-763 **1 In Stock**

- 1 + €780^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€780,00 each
Qty 5+	€741,30 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

No **NST Certification:**

Physical & Mechanical Properties

Metric: 25µm
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

Thickness (mm):
1.50 ±0.100

Dimensional Tolerance (mm):
±0.100

Optical Properties

Chrome on Opal Glass Substrate:

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

