

Fiber Optic Cutting Block



Stock #54-013 **7 In Stock**

⊖ 1 ⊕ €46⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€46,00 each
Qty 5+	€40,75 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Cleaves Jacketed and Unjacketed Fiber

- Accepts Fiber up to 3300µm Diameter
- Blade Included

Fiber Optic Cutting Blocks use tight tolerance guide holes to position fibers for cutting with standard blades (included). Jacketed andunjacketed fibers maybe cleaved with this instrument: from 750 to 3000 micron unjacketed, 750 to 1500 micron jacketed (includes duplex fibers), and all 265 micron fiber bundles. Holes accept 750 to 3300 micron outer diameters. The Fiber Optic Cutting Block features a $90^{\circ} \pm 0.2^{\circ}$ cutting angle. Cutting block included with Optical Fiber Hot Knife [#54-014](#).
