

Fiber Optic Taper For 18mm to 11mm



Stock **#55-135** 3-4 DAYS

-

1

+

€1.161,00

ADD TO CART

Qty 1+
€1.161,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter Tolerance (mm): ±0.5, Large End
Distortion (%): 3.00
Substrate: Schott 24 Glass with EMA
Height (mm): 15.25
Diameter of Large End (mm): 20.00

Numerical Aperture NA: 1.00
Operating Temperature (°C): -10 to +300
Resolution: 102 lp/mm
Size Ratio: 18:11 mm
Size of Small End (mm): 12.50
Surface Quality: 30-20
Thickness Tolerance (mm): ±0.1
Resolving Power (μm): 6.00
Dimensional Tolerance (mm): ±0.1
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.8
Core/ Clad Ratio: 70 / 30

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View