

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #58-874 3-4 DAYS



1



€118,00

ADD TO CART

Qty 1-4

€118,00

Qty 5+

€106,20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Square or Rectangular

Size of Compatible Optics (mm):
12.7 - 101.6

Number of Adjustment Screws:

Aperture Size: 1" (25mm)
Thickness of Compatible Optics (mm): 0.5 - 3.7
Travel (mm): No Z-Axis Translation
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Pointing Stability (μrad): 1.3
Aperture Size (mm): 25.0

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View