

3/4" Dia Stainless Posts, Vertical Post 18"



Stock **#39-353** 9 In Stock

-

1

+

€108^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€108,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounting Post	Type:
---------------	-------

Physical & Mechanical Properties

457.2	Length (mm):
1.75	Weight (lbs):
18.0	Length (inches):

3/4	Diameter (inches):
Threading & Mounting	
3/4-16 Male (One End)	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Posts for Integration into Imaging Systems
 - Vertical Posts Thread to Bases and Platforms
 - Horizontal Arms Thread to Posts and Microscope Head Mounts
 - [Rack and Pinion Focusing Mounts](#), and [Accessories](#) also Available
- Stainless Steel Posts for Imaging Systems are used for constructing and supporting imaging systems. Vertical posts can be threaded directly into bases or platforms and include a steel collar with a set screw. Horizontal arms can be used with a 90° angle mount, on vertical posts, or with a breadboard adapter. Stainless Steel Posts for Imaging Systems are ¾ of an inch in diameter and are offered in lengths ranging from 9.0 inches (228.6mm) to 24.0 inches (609.6mm). The mounting threads for these posts are available threaded on one end with ¾"-16 male or threaded on both ends with a combination of ¼"-20 and 5/16"-18 pins.