

SCHOTT GG-400, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-423** 3-4 DAYS

- 1 + **€38,75**

ADD TO CART

Qty 1-10
€38,75
Qty 11+
€38,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
400±6

Cut-On Wavelength (nm): 400.00
Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG400
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 480.00
Passband Limit 2 λ_{p2} (nm): 700.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s(nm): 340.00
Surface Quality: 80-50
Transformation Temperature (°C): 537.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View