

[See all 3 Products in Family](#)

## Adjustable Grating Mount Adapter for 20-40mm Optic



Stock #18-538 **7 In Stock**

⊖ 1 ⊕ €173<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€173,00 each
Qty 10+	€164,40 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Fixed **Type:**

Square or Rectangular **Type of Optics:**

Includes Hex Wrench for Locking Screws **Note:**

Compatible Kinematic Mount:  
[#15-866](#), [#58-851](#), [#58-854](#)

## Threading & Mounting

Size of Compatible Optics (mm):  
20.0 - 40.0

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

## Product Details

- Mount up to 60mm Tall Diffraction Gratings
- Easy Adjustment via Side Locking Screws
- Designed for Integration into 25.4mm Diameter Optic Mounts

Adjustable Grating Mounts are designed to hold diffraction gratings without damaging their sensitive grating surface. Featuring a 3-point mounting style with spring and metal contacts, these mounts provide adequate clamping pressure while allowing for easy adjustment via side locking screws. A 25.4mm diameter extension on the rear of the mount allows for integration into [TECHSPEC® Kinematic Mounts](#), [E-Series Circular Kinematic Mounts](#), and [fixed mirror mounts](#). Adjustable Grating Mounts can be adjusted to accommodate a range of grating sizes, up to 60mm in height.