

High Output Cylindrical Type Spot Light HLV3-22BL-4C



Stock #21-867 3-4 DAYS

- 1 + **€717,00**

ADD TO CART

Qty 1+
€717,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color: Blue
Model Number: HLV3-22BL-4C
Dimensions (mm): Outer diameter 22 mm, Tip diameter 8 mm, Total length 61 mm
Wavelength (nm): 465.00
Weight (g):

39
Power Consumption (W): 3.8
Active Area (mm): 6
Type of Illumination: LED Illuminator
Manufacturer: CCS
Geometry: Spot Light
Maximum Input Current: 1000mA
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
