

# Hoya B390 (UV-VIS) 25.4mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-782** 3-4 DAYS

[Additional Bandwidths](#)

- 1 + **€63,00**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| €63,00   |

|         |
|---------|
| Qty 11+ |
| €56,00  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.40

|                                                      |
|------------------------------------------------------|
| Center Wavelength CWL (nm):<br>390.00                |
| Density (g/cm³):<br>2.57                             |
| Full Width-Half Max FWHM (nm):<br>125.00             |
| Glass/Filter Number:<br><a href="#">Hoya B390</a>    |
| Substrate: <input type="checkbox"/><br>Colored Glass |
| Coating:<br>Uncoated                                 |
| Color:<br>Blue-Violet                                |
| Surface Quality:<br>60-40                            |
| Thickness (mm):<br>1.00                              |
| Thickness Tolerance (mm):<br>±0.1                    |
| Type:<br>Bandpass Filter                             |
| Wavelength:<br>UV-VIS                                |
| Parallelism (arcmin):<br>≤2                          |
| Dimensional Tolerance (mm):<br>±0.2                  |

### Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |