

Hoya IR85N (850nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-904 3-4 DAYS

⊖

1

⊕

€32,00

ADD TO CART

Qty 1-10

€32,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
850.00 ±10

Density (g/cm³):
490

Glass/Filter Number: Hoya IR85N	
Substrate: ☐ Colored Glass	
Coating: Uncoated	
Color: Black	
Surface Quality: 60-40	
Transformation Temperature (°C): 3.02	
Thickness (mm): 2.50	
Thickness Tolerance (mm): ±0.1	
Type: Longpass Filter	
Wavelength: IR	
Dimensional Tolerance (mm): ±0.2	
Reflection Factor P _d : 0.91	
Bevel: Protective as needed	
Δλ (nm): <60	
TH (%): N/A	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	