

Hoya L38 (380nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-836 3-4 DAYS

⊖

1

⊕

€88,00

ADD TO CART

Qty 1-10
€88,00

Qty 11+
€78,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
380.00 ±5

Density (g/cm³):
2.96

Glass/Filter Number: Hoya L38	
Substrate: ☐ Colored Glass	
Coating: Uncoated	
Color: Clear	
Surface Quality: 60-40	
Transformation Temperature (°C): 480	
Thickness (mm): 2.50	
Thickness Tolerance (mm): ±0.1	
Type: Longpass Filter	
Wavelength: UV	
Dimensional Tolerance (mm): ±0.2	
Reflection Factor P _d : 0.91	
Bevel: Protective as needed	
Δλ (nm): <35	
TH (%): >85	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	