

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Hoya R70 (700nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-892 3-4 DAYS

1

€88,00

ADD TO CART

Qty 1-10

€88,00

Qty 11+

€78,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
700.00 ±10

Density (g/cm³):
2.86

Glass/Filter Number: Hoya R70
Substrate: Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Transformation Temperature (°C): 525
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed
Δλ (nm): <45
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View