

Hoya UV28N (280nm), 25.4mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-793 3-4 DAYS

-

1

+

€44,00

ADD TO CART

Qty 1-10

€44,00

Qty 11+

€39,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Cut-On Wavelength (nm):
280.00 ±7

Density (g/cm³):
2.61

Glass/Filter Number: Hoya UV28N	
Substrate: ☐ Colored Glass	
Coating: Uncoated	
Color: Clear	
Surface Quality: 60-40	
Transformation Temperature (°C): 572	
Thickness (mm): 1.00	
Thickness Tolerance (mm): ±0.1	
Type: Longpass Filter	
Wavelength: UV	
Dimensional Tolerance (mm): ±0.2	
Reflection Factor P _d : 0.92	
Bevel: Protective as needed	
Δλ (nm): <45	
TH (%): >85	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	