

# Hoya UV34N (340nm), 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-815 3-4 DAYS

-

1

+

**€32,00**

ADD TO CART

Qty 1-10

€32,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
12.50

**Cut-On Wavelength (nm):**  
340.00 ±7

**Density (g/cm³):**  
4.01

|                                                                |
|----------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">Hoya UV34N</a></div> |
| <div>Substrate: <div></div><br/>Colored Glass</div>            |
| <div>Coating:<br/>Uncoated</div>                               |
| <div>Color:<br/>Clear</div>                                    |
| <div>Surface Quality:<br/>60-40</div>                          |
| <div>Transformation Temperature (°C):<br/>447</div>            |
| <div>Thickness (mm):<br/>1.00</div>                            |
| <div>Thickness Tolerance (mm):<br/>±0.1</div>                  |
| <div>Type:<br/>Longpass Filter</div>                           |
| <div>Wavelength:<br/>UV</div>                                  |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>                |
| <div>Reflection Factor P<sub>d</sub>:<br/>0.88</div>           |
| <div>Bevel:<br/>Protective as needed</div>                     |
| <div>Δλ (nm):<br/>&lt;35</div>                                 |
| <div>TH (%):<br/>&gt;85</div>                                  |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |