

[See all 53 Products in Family](#)

IDS GV-5040FA-M-GL, GigE, 1/2.9" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock #26-288 **1 In Stock**

⊖ 1 ⊕ €775.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€775,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

GV-5040FA-M-GL **Model Number:**

Manufacturer:
IDS Imaging Development Systems

Camera Series:
uEye+ FA

Physical & Mechanical Properties

Dimensions (mm):
41 x 53 x 42.7 (excludes connectors and lens mount)

Weight (g):
173

Housing:
Full

Sensor

Image Buffer:
128MB

Sensor Format:
1/2.9"

Resolution (Megapixels):
1.58

Frame Rate (fps):
78.00

Pixels (H x V):
1,448 x 1,086

Pixel Size, H x V (µm):
3.45 x 3.45

Sensing Area, H x V (mm):
4.995 x 3.746

Imaging Sensor:
Sony IMX273

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
12 bit

Exposure Time:
0.025ms - 2000ms

Dynamic Range (dB):
70.00

Machine Vision Standard:
GigE Vision

Electrical

Power Consumption (W):
1.4 - 3.1

Hardware & Interface Connectivity

Interface:
GigE (PoE)

Connector:
GigE M12, screwable

Power Supply:
Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#19-692](#)

GPIOs:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground

Synchronization:
Hardware Trigger (GPIO); Software Trigger

Interface Port Orientation:
Back Panel

GPIO Connector Type:
8-pin Binder connector (Binder series 712: 09-0427-020-08)

Threading & Mounting

Mount:
C-Mount

Mounting Threads:
¼-20 with Tripod Mount Adapter [#19-694](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +55

-20 to +60

Storage Temperature (°C):

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.