

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



IDS Imaging uEye LE USB 3.1 AF Autofocus Liquid Lens Board Level Cameras (M12 S-Mount)



Stock #24-096 3-4 DAYS

[Similar Cameras](#)



1



€580,00

ADD TO CART

Qty 1+

€580,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
IDS Imaging

Mounting Threads: No Mounting Threads/Tripod Adapter
Image Buffer: Not Specified
Camera Family: uEye LE
Model Number: U3-3861LE-C-HQ-AF Rev.1.2
Imaging Sensor: Sony IMX290
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 2.10
Pixels (H x V): 1,936 x 1,096
Pixel Size, H x V (µm): 2.90 x 2.90
Sensing Area, H x V (mm): 5.61 x 3.17
Frame Rate (fps): 135.00
Pixel Depth: 12 bit
Exposure Time: 11µs - 1.7s
Connector: USB Type-C
Power Supply: Power over USB
Power Consumption (W): 1 - 1.5
GPIOs: 2 Flash Output, 2 Trigger Input, 2 GPIO, 2 TWI, 1 Voltage Output, 1 Ground
Synchronization: Hardware Trigger (GPIO); Software Trigger
Dimensions (mm): 36 x 36 x 20 (excludes connectors and lens mount)
Weight (g): 15
Mount: M12 x 0.5 (S-Mount)
Housing: Board Level
Interface Port Orientation: Back Back (Right Angle)
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +55
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 10-pin Wuerth
Machine Vision Standard: USB3 Vision v1.1

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View