

[See all 32 Products in Family](#)

IDS U3-3864LE-C-HQ, USB 3.0, 1/2.8" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Board Level, Front View)



Stock #24-126 **1 In Stock**

[Similar Cameras](#)

- 1 + €395.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€395,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

Model Number:

U3-3864LE-C-HQ

Manufacturer:
IDS Imaging Development Systems

Camera Series:
uEye+ LE

Note:
Ships with an adapter to convert to C- or CS-Mount

Physical & Mechanical Properties

Dimensions (mm):
36 x 36 x 20 (excludes connectors and lens mount)

Weight (g):
18

Housing:
Board Level

Sensor

Image Buffer:
Not Specified

Sensor Format:
1/2.8"

Resolution (Megapixels):
2.10

Frame Rate (fps):
135.00

Pixels (H x V):
1,936 x 1,096

Pixel Size, H x V (µm):
2.90 x 2.90

Sensing Area, H x V (mm):
5.61 x 3.175

Imaging Sensor:
Sony IMX290

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Rolling

Pixel Depth:
12 bit

Exposure Time:
0.02ms - 1649ms

Dynamic Range (dB):
72.00

Machine Vision Standard:
USB3 Vision

Electrical

Power Consumption (W):
1 - 1.5

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB Type-C

Power Supply:
Power over USB

GPIOs:
2 Flash Output, 2 Trigger Input, 2 GPIO, 2 TWI, 1 Voltage Output, 1 Ground

Synchronization:
Hardware Trigger (GPIO); Software Trigger

Interface Port Orientation:
Back Panel (Right Angle)

GPIO Connector Type:
10-pin Wuerth connector (WR-WTB 1.00 mm)

Threading & Mounting

Mount:
C/CS-Mount

Mounting Threads:
N/A

Environmental & Durability Factors

Operating Temperature (°C):

0 to +55

Storage Temperature (°C):

-20 to +80

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.
