

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock #16-866 3-4 DAYS



1



€1.205,00

ADD TO CART

Qty 1+

€1.205,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1739.13

Groove Density Uniformity (grooves/mm):
0.001

Design Wavelength DWL (nm):
1030 ±10

Minimum Efficiency (%) : ≥94 @ 1030nm
Dimensions (mm) : 31.80 x 20.20
Angle of Incidence (°) : 63.6 ±1
Clear Aperture CA (mm) : 30.80 x 19.20
Coating : Dielectric
Construction : Multi-Layer Dielectric Binary Etch Grating
Length (mm) : 31.80
Model Number : 1379487
Substrate :  Fused Silica (Corning 7980)
Surface Quality : 60-40
Thickness (mm) : 0.95 ±0.050
Type : Transmission Diffraction Grating
Width (mm) : 20.20
Alignment of Grooves to Edge (°) : 0.1 (typical)
Polarization : S
Note : S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View