

[See all 6 Products in Family](#)

Infiniprobe N-32 UV Right Angle Video Microscope

See More by [Infinity Photo-Optical Company](#)



Stock **#62-854** [CONTACT US](#)

- 1 + €4.130⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€4.130,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Long Distance Microscope

Style:

UV, Right Angle

Physical & Mechanical Properties

Length (mm):

100.00

Maximum Diameter (mm):

78.5	
181.4	Weight (g):
Optical Properties	
2.75mm	Horizontal Field of View, 2/3" Sensor:
2.0mm	Horizontal Field of View, 1/2" Sensor:
0X- 3.2X	Primary Magnification PMAQ:
32 - ∞	Working Distance (mm):
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Available in Standard and Right Angle Versions
- Magnification Range from 0X to 8.0X
- Max 2/3" Sensor Format
- Direct Video C-Mount Coupling
- No Adapters Required

The InfiniProbe™ is available in a model designed to continuously focus UV light. The InfiniProbe™ 8.0X UV Video Microscope boasts a magnification range of 0-8X, supports up to a 2/3" format sensor, and offers direct video C-Mount coupling while incorporating exceptional resolution in the UV spectrum. Focusing from infinity down to a 0.8mm FOV at a WD of 20mm, the InfiniProbe™ 8.0X UV is capable of yielding magnifications up to 328X on a 13 inch monitor (based on a 1/2" sensor). To double magnification, add the DL-UV (#58-947) or LDL-UV (#58-948) Doubler Tube on the C-Mount. Mounting is provided through an included 1/4-20 mounting clamp. A variety of UV lighting options are available including the [MH-100 illuminator](#), [UV curing lamps](#), and [Broadband Fiber Coupled Illuminators](#).

Technical Information

