

Infiniprobe S-80 UV Video Microscope

See More by [Infinity Photo-Optical Company](#)



Stock #58-946 [CONTACT US](#)

⊖ 1 ⊕ €4.530⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€4.530,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Long Distance Microscope **Type:**

UV **Style:**

Physical & Mechanical Properties

180.00 **Length (mm):**

Maximum Diameter (mm):

184.3 **Weight (g):**

Optical Properties

1.1mm **Horizontal Field of View, 2/3" Sensor:**

0.8mm **Horizontal Field of View, 1/2" Sensor:**

0X- 8.0X **Primary Magnification PMAG:**

20 - ∞ **Working Distance (mm):**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

C-Mount **Mount:**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 224:**

View **Certificate of Conformance:**

Product Details

- Available in Standard and Right Angle Versions
- Magnification Range from 0X to 8.0X
- Max 2/3" Sensor Format
- Direct Video C-Mount Coupling
- No Adapters Required

The InfiniProbe™ is available in a model designed to continuously focus UV light. The InfiniProbe™ 8.0X UV Video Microscope boasts a magnification range of 0-8X, supports up to a 2/3" format sensor, and offers direct video C-Mount coupling while incorporating exceptional resolution in the UV spectrum. Focusing from infinity down to a 0.8mm FOV at a WD of 20mm, the InfiniProbe™ 8.0X UV is capable of yielding magnifications up to 328X on a 13 inch monitor (based on a 1/2" sensor). To double magnification, add the DL-UV (#58-947) or LDL-UV (#58-948) Doubler Tube on the C-Mount. Mounting is provided through an included 1/4-20 mounting clamp. A variety of UV lighting options are available including the [MH-100 illuminator](#), [UV curing lamps](#), and [Broadband Fiber Coupled Illuminators](#).

Technical Information

InfiniProbe™ UV Video Microscopes Standard Configuration

