

IR 940nm, MicroBrite LED Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination MicroBrite Spot Light

Stock **#18-601** 3-4 DAYS

-

1

+

€329,00

ADD TO CART

Qty 1+

€329,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
IR

Diameter (mm):
7.90

Fiber Bundle Diameter (inches):
1/4

Model Number:
SL223-940IC

Length (mm): 38.10
Operating Temperature (°C): 0 - 50
Outer Diameter (inches): 0.312
Wavelength (nm): 940.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant
Environmental Rating: IP65

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)