

IR M105 x 1.00 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-612** [CONTACT US](#)

⊖ 1 ⊕ **€728,00**

ADD TO CART

Qty 1-9

€728,00

Qty 10+

€691,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-782

Clear Aperture CA (mm):
100.00

Coating:
Hard Coated

Filter Thread: M105 x 1.00
Color: IR
Center Wavelength CWL (nm): 850.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 160.00
Mount Thickness (mm): 5.7
Mount Thickness Including Threads (mm): 8.5
Outer Diameter (mm): 109.80
Substrate Thickness (mm): 1.8
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
