

Light Red M43 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-695 3-4 DAYS



1



€153,00

ADD TO CART

Qty 1-9

€153,00

Qty 10+

€145,70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-570, 700-1117

Clear Aperture CA (mm):
38.00

Coating:
Hard Coated

Filter Thread: M43 x0.75
Color: Light Red
Center Wavelength CWL (nm): 635.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 60.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 45.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
