

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #21-813 3-4 DAYS



1



€1.544,00

ADD TO CART

Qty 1+

€1.544,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Input Voltage (V):
24

Model Number:
FPQ3-120SW

Dimensions (mm):
W 120 mm x D 120 mm x H 30 mm

Weight (g):
220

Power Consumption (W):
27

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#66-855](#)
Korea: [#33-733](#)
China: [#66-855](#)

Color Temperature (K):
6000

Type of Illumination:
LED Illuminator

Manufacturer:
CCS

Geometry:
Low-Angle Square Light

Illumination Mode:
Constant

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)