


# LUCID Vision Labs Atlas™ ATL071S-CC, Sony IMX420, 7.1MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Atlas™ Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras

Stock #17-111 3-4 DAYS

- 1 + **€2.329,00**

ADD TO CART

Qty 1+

€2.329,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Video Output:**  
5GigE (PoE)

**Type:**  
Color Camera

**Manufacturer:**  
Lucid Vision Labs

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#13-751](#)

|                                                                                                                                                                                                                                   |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Image Buffer:</b><br>380MB                                                                                                                                                                                                     |
| <b>Camera Family:</b><br>Atlas™                                                                                                                                                                                                   |
| <b>Model Number:</b><br>ATL071S-CC                                                                                                                                                                                                |
| <b>Imaging Sensor:</b><br>Sony IMX420                                                                                                                                                                                             |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                                                                                                                                                                   |
| <b>Type of Shutter:</b><br>Global                                                                                                                                                                                                 |
| <b>Camera Sensor Format:</b><br>1.1"                                                                                                                                                                                              |
| <b>Resolution (MegaPixels):</b><br>7.10                                                                                                                                                                                           |
| <b>Pixels (H x V):</b><br>3,208 x 2,200                                                                                                                                                                                           |
| <b>Pixel Size, H x V (µm):</b><br>4.5 x 4.5                                                                                                                                                                                       |
| <b>Sensing Area, H x V (mm):</b><br>14.44 x 9.90                                                                                                                                                                                  |
| <b>Frame Rate (fps):</b><br>74.60                                                                                                                                                                                                 |
| <b>Pixel Depth:</b><br>8/10/12 bit                                                                                                                                                                                                |
| <b>Exposure Time:</b><br>13.7µs - 10s                                                                                                                                                                                             |
| <b>Connector:</b><br>5GigE, M12                                                                                                                                                                                                   |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#18-364</a><br>Europe: <a href="#">#18-364</a><br>Japan: <a href="#">#18-364</a><br>Korea: Not Available<br>China: <a href="#">#18-364</a> |
| <b>Power Consumption (W):</b><br>7 (External Power Supply) 8 (PoE)                                                                                                                                                                |
| <b>GPIOs:</b><br>1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports                                                                                                                               |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)                                                                                                                                          |
| <b>Dimensions (mm):</b><br>55 x 55 x 70 (excludes connectors and lens mount)                                                                                                                                                      |
| <b>Weight (g):</b><br>240                                                                                                                                                                                                         |
| <b>Mount:</b><br>C-Mount                                                                                                                                                                                                          |
| <b>Housing:</b><br>Full                                                                                                                                                                                                           |
| <b>Interface Port Orientation:</b><br>Back Panel                                                                                                                                                                                  |
| <b>Dynamic Range (dB):</b><br>71.92                                                                                                                                                                                               |
| <b>Operating Temperature (°C):</b><br>-20 to +55                                                                                                                                                                                  |
| <b>Storage Temperature (°C):</b><br>-30 to +60                                                                                                                                                                                    |
| <b>GPIO Connector Type:</b><br>8-pin M8                                                                                                                                                                                           |
| <b>Machine Vision Standard:</b><br>GigE Vision v2.0                                                                                                                                                                               |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |