

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Lumenera INFINITY 3-60K Microscopy Color Camera

See More by [Teledyne DALSA](#)



Stock #33-289 3-4 DAYS



1



€6.000,00

ADD TO CART

Qty 1+

€6.000,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:  
USB 3.0

Type:  
Color Microscopy Camera

Manufacturer:  
Teledyne Lumenera

Mounting Threads:

|                                                                     |
|---------------------------------------------------------------------|
| 2 x ¼-20 (Integrated into Housing)                                  |
| <b>Image Buffer:</b><br>Not Specified                               |
| <b>Camera Family:</b><br>INFINITY                                   |
| <b>Model Number:</b><br>INFINITY3-6UR                               |
| <b>Imaging Sensor:</b><br>Sony ICX694                               |
| <b>Type of Sensor:</b><br>Progressive Scan CCD                      |
| <b>Type of Shutter:</b><br>Global                                   |
| <b>Camera Sensor Format:</b><br>1"                                  |
| <b>Resolution (MegaPixels):</b><br>6.00                             |
| <b>Pixels (H x V):</b><br>2,752 x 2,192                             |
| <b>Pixel Size, H x V (µm):</b><br>4.54 x 4.54                       |
| <b>Sensing Area, H x V (mm):</b><br>12.49 x 9.95                    |
| <b>Frame Rate (fps):</b><br>27.00                                   |
| <b>Pixel Depth:</b><br>8/14 bit                                     |
| <b>Exposure Time:</b><br>23µs - 1.79s (video)                       |
| <b>Power Supply:</b><br>Power over USB                              |
| <b>Power Consumption (W):</b><br>6                                  |
| <b>GPIOs:</b><br>N/A                                                |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO)                  |
| <b>Dimensions (mm):</b><br>97.8 x 69.8 x 50.8 (excludes lens mount) |
| <b>Weight (g):</b><br>395                                           |
| <b>Mount:</b><br>C-Mount                                            |
| <b>Housing:</b><br>Full                                             |
| <b>Interface Port Orientation:</b><br>Side Panel                    |
| <b>Dynamic Range (dB):</b><br>68.6                                  |
| <b>Operating Temperature (°C):</b><br>0 to +50                      |
| <b>Storage Temperature (°C):</b><br>-30 to +70                      |
| <b>GPIO Connector Type:</b><br>8-pin Hirose (MRX)                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |