

M35.5 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x 0.5 to T-Mount Step-Up Adapter, #12-481

Stock **#12-484** **5 In Stock**

⊖ 1 ⊕ €34²⁵

ADD TO CART

Volume Pricing	
Qty 1-9	€34,25 each
Qty 10-25	€30,90 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Filter Adapter	Type:
M42 x 0.75 (T-Mount)	Inner Thread:
M35.5 x 0.5	Outer Thread:
48.0	Outer Diameter (mm):
	Thread Type:

T-Mount to M35.5 x0.5

Clear Aperture CA (mm):
32.5

Mount Thickness (mm):
5.5

Total Thickness with Thread (mm):
8.0

Function:
Thread Adapter

Note:
Filter Sold Separately

Regulatory Compliance

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

Product Details

- Integrate C and T-Mount Components into Imaging Systems
- Compatible with M22.5 to M40.5 Machine Vision Threads
- Step-Up Design Prevents Vignetting

Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.

;