

M37.5 x 0.50 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-681 3-4 DAYS

⊖ 1 ⊕ **€76,50**

ADD TO CART

Qty 1-9
€76,50

Qty 10+
€73,30

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
32.50

Coating:
Hardcoated

Diameter (mm):
39.50

Extinction Ratio:

up to 3000:1 @~600nm (nominal)

Filter Thread:
M37.5 x0.50

Surface Quality:
40-20

Type:
Mounted Imaging Filter

Construction:
Black Anodized Aluminum

Wavelength Range (nm):
400 - 700

Mount Thickness Including Threads (mm):
9.6

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)